



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
LC1D50AG7

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 50A
 UL File/CCN: E164862 / NLDX
 CSA File: LR43364 3211 04
 Meets Standards: IEC 60647-4
 Weight: 2.29 lb (0.855 kg)
 Termination Method: Screw Clamp
 Wire Size: Power: #2 - #16 AWG
 Control: #12 - #20 AWG
 Terminal torque: Power: 70 lb-in (8 Nm)
 Control: 8 lb-in (0.9 Nm)
 Mounting Hwd.: 35mm DIN Rail, #8 screw

Specification:

Description: TeSys D IEC Contactor New Type with Everlink® - 50A - Vac Coil
 Type: TeSys D IEC Contactor - 50A - 120Vac Coil
 Voltages Code: G7 at 120Vac 50/60 Hz

Coil Consumption: Inrush 160 VA
 Sealed 15 VA

| Single Phase | | | Three Phase | | |
|--------------|--------|-------|-------------|-------|-------|
| 115V | 230V | 200V | 230V | 460V | 575V |
| 3 HP | 7.5 HP | 15 HP | 15 HP | 40 HP | 40 HP |