



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

LC1D65N7



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 65A
 UL File/CCN: E164862 / NLDX
 CSA File: LR43364 3211 04
 Meets Standards: IEC 60647-4
 Weight: 3.11 lb (1.41 kg)
 Termination Method: Screw Clamp
 Wire Size: Power: #4 - #16 AWG
 Control: #10 - #18 AWG
 Terminal torque: Power: 45 lb-in (5 Nm)
 Control: 15 lb-in (1.7 Nm)
 Mounting Hwd.: 35mm DIN Rail, #8 screw

Specification:

Description: Old Type TeSys D IEC Contactor - 65A - Vac Coil
 Type: TeSys D IEC Contactor - 65A - 415Vac Coil
 Voltages Code: N7 at 415Vac 50/60 Hz

Coil Consumption: Inrush 220 VA
 Sealed 22 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
5 HP	10 HP	20 HP	20 HP	40 HP	50 HP