



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

LJA36400-Electronic



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Certification: UL Listed, CSA, IEC Rated
 Mounting Type: I-Line
 Weight: 19
 AL Lug Wire Size A,L,M,P:
 Depth:
 Height:
 Width:

Specification:

Description: I-Line - 3 Pole Molded Case Circuit Breaker
 General Application: Provides overload and short circuit protection
 For Use With: I-line Panelboards and Switchboards
 Voltage Rating: N/A
 Ampere Rating: 400A
 Electronic Trip Unit Function: LI, LS, LSI, or LSIG
 Number of Poles: 3
 Short Circuit Current Rating: 100/65/25 kA UL and IEC ratings
 Circuit Breaker Rating: Standard 80%