



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

MGL36300



by **Schneider Electric**

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone: +1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
For Use With: Industrial Enclosures and Switchboards
Approvals: UL Listed - CSA Certified - IEC Rated
Mounting Type: Unit Mount
Terminal Type: Line: Lug - Load: Lug
Wire Size: (3) 3/0 through 500 kcmil Al or Cu
Weight:
Depth: 8.06 Inches
Height: 12.86 Inches
Width: 8.27 Inches

Specification:

Description: PowerPact M-frame Molded Case Circuit Breaker
Number of Poles: 3-Pole
Ampere Rating: 300A
Voltage Rating: 600VAC
Interrupting Rating: 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC
Circuit Breaker Rating: 80% Rated