


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

NSYEBAD11614



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Copper Wire
 0.09
 5/32 Hex
 5/64 Hex
 E323110 QPQS
 N/A
 File 70361, Class 6228-01 (With wire classes B&C)
 Yes
 Yes
 Yes
 UL 94 V0

Description:
Mounting:
Ampere Rating:
Max. Voltage Rating:
Terminal Material:
 Wire Range - Line Side AWG/kcmil:
 Wire Range - Load Side AWG/kcmil:
 Short Circuit Current Ratings with Fuses:

Specification:

Enclosed Power Distribution Block
 35 mm DIN rail or Panel
 115 Amps CU
 600V AC/DC
 Tin Plated Aluminum
 14-2 CU
 14-10 CU
 Up to 65kA

Type Wire:
 Weight (lb):
 Terminal Screw Driver Line Side:
 Terminal Screw Driver Load Side:
 UL Listed:
 UL Recognized:
 CSA File:
 RoHS:
 CE Marked:
 IP20 Touch Protection from the Front
 Flammability Rating: