



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**NSYEBCD12611**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Type Wire:  
 Weight (lb):  
 Terminal Screw Driver Line Side:  
 Terminal Screw Driver Load Side:  
 UL Listed:  
 UL Recognized:  
 CSA File:  
 RoHS:  
 CE Marked:  
 IP20 Touch Protection from the Front  
 Flammability Rating:

**Technical Information:**  
 Copper Wire  
 0.55  
 6 mm Hex  
 6 mm Hex  
 E323110 QPQS  
 N/A  
 File 70361, Class 6228-01 (With wire classes B&C)  
 Yes  
 Yes  
 Yes  
 UL 94 V0

**Description:**  
 Mounting:  
 Ampere Rating:  
 Max. Voltage Rating:  
 Terminal Material:  
 Wire Range - Line Side AWG/kcmil:  
 Wire Range - Load Side AWG/kcmil:  
 Short Circuit Current Ratings with Fuses:

**Specification:**  
 Enclosed Power Distribution Block  
 35 mm DIN rail  
 200 Amps CU  
 600V AC/DC  
 Tin Plated Copper  
 14 - 3/0 CU  
 14 - 3/0 CU  
 Up to 100kA