



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
NSYEBCP12614

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Type Wire:	Copper Wire
Weight (lb):	0.53
Terminal Screw Driver Line Side:	6 mm Hex
Terminal Screw Driver Load Side:	5 mm Hex
UL Listed:	E323110 QPQS
UL Recognized:	N/A
CSA File:	File 70361, Class 6228-01 (With wire classes B&C)
RoHS:	Yes
CE Marked:	Yes
IP20 Touch Protection from the Front	Yes
Flammability Rating:	UL 94 V0

Description:

Mounting:	Panel
Ampere Rating:	200 Amps CU
Max. Voltage Rating:	600V AC/DC
Terminal Material:	Tin Plated Copper
Wire Range - Line Side AWG/kcmil:	14 - 3/0 CU
Wire Range - Load Side AWG/kcmil:	14 - 2 CU
Short Circuit Current Ratings with Fuses:	Up to 100kA

Specification:

Enclosed Power Distribution Block
Panel
200 Amps CU
600V AC/DC
Tin Plated Copper
14 - 3/0 CU
14 - 2 CU
Up to 100kA