

# Product data sheet

## Characteristics

# NSYSBM20608

Metal industrial box plain door H200xW600xD80  
IP66 IK10 RAL 7035

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 154.36 USD



### Main

Range	PanelSeT
Product name	PanelSeT SBM
Device Application	Multi-purpose
Product or Component Type	Industrial box
Device short name	SBM
Enclosure Type	Flat face box
Enclosure nominal height	7.9 In (200 mm)
Enclosure nominal width	23.6 In (600 mm)
Enclosure nominal depth	3.1 In (80 mm)
Enclosure mounting	Wall mounted
Device composition	1 cover 1 body 6 cover screw
Body type	Single piece body folded and welded
Type of front cover	Plain door
Cover fixing	Half turn metal screw
Lock type	Captive screw PZ2 outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	Sheet steel
Surface Finish	Polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	DNV-GL[RETURN]UL[RETURN]BV
IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient Air Temperature for Storage	-31...140 °F (-35...60 °C)
Ambient Air Temperature for Operation	-31...176 °F (-35...80 °C)
Product Weight	9.37 Lb(US) (4.25 kg)

## Ordering and shipping details

Category	US10ES180033
Discount Schedule	0ES1
GTIN	3606480520099
Returnability	No
Country of origin	IN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.94 In (10.000 cm)
Package 1 Width	8.66 In (22.000 cm)
Package 1 Length	24.41 In (62.000 cm)
Package 1 Weight	9.370 Lb(US) (4.250 kg)
Unit Type of Package 2	P12
Number of Units in Package 2	18
Package 2 Height	23.62 In (60.000 cm)
Package 2 Width	31.50 In (80.000 cm)
Package 2 Length	47.24 In (120.000 cm)
Package 2 Weight	198.416 Lb(US) (90.000 kg)

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**