



Commercial status

End-of-Sale Notice : JAN 11, 2023

 End-of-Sale Notice

Main

Range	Exiway
Product name	Exiway Smartbeam Activa
Product or component type	Emergency luminaire
Device application	Lighting
Function	Self-test
Supply	Non-maintained Maintained
Number of batteries	1 x 3.2 V 1.5 Ah LiFePO4
Light source	1 x LED 10 W

Complementary

Mounting support	False ceiling
[Ue] rated operational voltage	230 V AC 50/60 Hz
Power consumption in VA	3.9 VA non-maintained 8.3 VA maintained
Power consumption in W	0.43 W non-maintained 3.5 W maintained
Electrical insulation class	Class II
Bulb lifespan	100000 H
Test function	Automatic periodical functional & duration test
Autonomy	1.5 h
Charging time	12 H
Illuminance	0.5 Lux
Material	Thermoplastic self-extinguishing
Height	55.8 Mm
Depth	23.8 Mm 31.5 Mm
Width	256.6 Mm
Diameter	90 Mm light fitting:
Net weight	292 G

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP42
IK degree of protection	IK04
Flame retardance	V2
Fire resistance	850 °C
Product certifications	ENEC[RETURN]CE
Ambient air temperature for operation	0...40 °C
Standards	EN 60598-1 EN 62034 UL 94 EN 60598-2-22 EN 62471: group 1 EN 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.2 Cm
Package 1 Width	5.0 Cm
Package 1 Length	28.0 Cm
Package 1 Weight	388.0 G
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Height	30.0 Cm
Package 2 Width	30.0 Cm
Package 2 Length	40.0 Cm
Package 2 Weight	4.283 Kg
Unit Type of Package 3	P06
Number of Units in Package 3	80
Package 3 Height	75.0 Cm
Package 3 Width	60.0 Cm
Package 3 Length	80.0 Cm
Package 3 Weight	41.0 Kg

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **End of commerc. - Block**

OVA48921 may be replaced by any of the following products:



OVA48953

Emergency luminaire, Exiway Smartbeam Activa Dicube, recessed, open area, 1.5h, 220lm, IP42, white
Qty 1

Substitution date: |