



### Main

Range	Exiway
Product name	Exiway Smartbeam Activa
Product or component type	Emergency light
Device application	Lighting
Function	Self-test
Supply	Non-maintained Maintained
Number of batteries	1 x 3.2 V 1.5 Ah LiFePO4
Light source	1 x LED 10 W

### Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Power consumption in VA	3.9 VA non-maintained 8.3 VA maintained
Power consumption in W	0.43 W non-maintained 3.5 W maintained
Electrical insulation class	Class II
Bulb lifespan	100000 H
Test function	Automatic periodical functional & duration test
Autonomy	1.5 h
Charging time	12 H
Illuminance	0.5 Lux
Device mounting	Flush false ceiling
Material	Thermoplastic self-extinguishing
Height	Driver: 55.8 mm
Depth	Driver: 23.8 mm Light fitting: 31.5 mm
Width	Driver: 256.6 mm
Diameter	90 Mm light fitting:
Net weight	292 G

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IP degree of protection	Light fitting: IP42 Driver: IP20
IK degree of protection	IK04
Flame retardance	V2
Fire resistance	850 °C
Product certifications	ENEC CE
Ambient air temperature for operation	0...40 °C
Standards	EN 60598-1 EN 62034 UL 94 EN 60598-2-22 EN 62471: group 1 EN 60695-2-10

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	388 G
Package 1 Height	18.2 Cm
Package 1 width	5 Cm
Package 1 Length	28 Cm
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Weight	4.283 Kg
Package 2 Height	30 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm
Unit Type of Package 3	P06
Number of Units in Package 3	80
Package 3 Weight	41 Kg
Package 3 Height	75 Cm
Package 3 width	60 Cm
Package 3 Length	80 Cm

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**