

Main

Range	Exiway
Product name	Exiway Smartbeam Activa
Product or component type	Emergency light
Device application	Lighting
Function	Self-test
Supply	Maintained Non-maintained
Number of batteries	1 x 3.2 V 1.5 Ah LiFePO4 battery
Light source	LED : 1 x 10 W

Complementary


[Ue] rated operational voltage	230 V at 50/60 Hz AC
Power consumption in VA	Non-maintained : 3.9 VA Maintained : 8.3 VA
Power consumption in W	Non-maintained : 0.43 W Maintained : 3.5 W
Electrical insulation class	Class II
Bulb lifespan	100000 h
Test function	Automatic periodical functional & duration test
Autonomy	1.5 h
Charging time	12 h
Luminous flux	190 lm
Illuminance	1 lux
Material	Self-extinguishing thermoplastic
Device mounting	Surface
Height	176 mm
Width	176 mm
Depth	53.5 mm
Product weight	479 g

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Flame retardance	V2
Fire resistance	850 °C

Product certifications	ENEC CE
Standards	EN 60695-2-10 EN 60598-2-22 EN 60598-1 UL 94 EN 62034 EN 62471: group 1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1810 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Product Life Status : **Commercialised**