



Commercial status
End-of-Sale Notice :

⚠ End-of-Sale Notice

Main

Range	Exiway
Product name	Exiway Smartbeam Activa
Product or component type	Emergency light
Device application	Lighting
Function	Self-test
Supply	Maintained Non-maintained
Number of batteries	1 x 3.2 V 1.5 Ah LiFePO4
Light source	1 x LED 10 W

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Power consumption in VA	3.9 VA non-maintained 8.3 VA maintained
Power consumption in W	0.43 W non-maintained 3.5 W maintained
Electrical insulation class	Class II
Bulb lifespan	100000 H
Test function	Automatic periodical functional & duration test
Autonomy	1.5 h
Charging time	12 H
Illuminance	1 Lux
Material	Thermoplastic self-extinguishing
Device mounting	Surface
Height	176 Mm
Width	176 Mm
Depth	53.5 Mm
Net weight	479 G

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Flame retardance	V2
Fire resistance	850 °C

Product certifications	ENEC CE
Standards	EN 60598-1 EN 62034 UL 94 EN 60598-2-22 EN 62471: group 1 EN 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	582 G
Package 1 Height	7 Cm
Package 1 width	20.2 Cm
Package 1 Length	18.2 Cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **End of commerc. - Block**