

I-LINE HCJ PANELBOARDS MEET THE APPLICABLE REQUIREMENTS

OF UL AND CSA.

BOX: CODE GAUGE STEEL WITH REMOVABLE BLANK ENDWALLS.

FRONT: CODE GAUGE STEEL. GRAY BAKED ENAMEL FINISH ELECTRODEPOSITED

OVER CLEANED PHOSPHATIZED STEEL.

LOCK: 73.00/[1854] - 91.00/[2311] HIGH FRONTS HAVE (2) FLUSH LOCKS WITH NSR-251 KEY.

FOR NEMA TYPE 3R APPLICATIONS USE IN CONJUNCTION WITH PBA475.

INCHES DUAL DIMENSIONS: **MILLIMETERS**

MAXIMUM MAIN BREAKER AMPERE RATING	BRANCH BREAKER MOUNTING SPACE (INCHES)	Н		A	
		IN	MM	IN	ММ
400	27	73.00	1854	47.10	1196
	45				
	81	91.00	2311	65.10	1654

JOB NAME:		EQUIPMENT DESIGNATION:	
JOB LOCATION:		EQUIPMENT TYPE:	I-LINE HCJ VERTICAL MCB
DRAWN BY:		DRAWING TYPE:	
ENGR:			SQUARE D
DATE:	FEBRUARY 2019		by Schneider Electric
DRAWING STATUS:		DWG# PBA471	PG 01 OF 01 REV —