


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**PGL36100CU74AE1**

  
 by **Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

<b>General Application:</b>	Provides overload and short circuit protection
<b>For Use With:</b>	Panelboards and Switchboards
<b>Approvals:</b>	UL Listed - CSA Certified - IEC Rated
<b>Mounting Type:</b>	Unit Mount
<b>Terminal Type:</b>	Lugs (ON and OFF ends)
<b>Wire Size:</b>	#3/0-500 AWG/kcmil(Al/Cu)
<b>Weight:</b>	32 Pounds
<b>Depth:</b>	8.07 Inches
<b>Height:</b>	16.26 Inches
<b>Width:</b>	8.27 Inches

**Specification:**

<b>Description:</b>	PowerPact P-frame Electronic Trip Circuit Breaker
<b>Number of Poles:</b>	3-Pole
<b>Sensor Rating:</b>	1000A
<b>Voltage Rating:</b>	600VAC
<b>Interrupting Rating:</b>	65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC
<b>Circuit Breaker Rating:</b>	100% Rated
<b>Electronic Trip Unit:</b>	Micrologic Harmonic Trip Unit (6.0H)
<b>Trip Function:</b>	LSIG
<b>Installed Rating Plug:</b>	Type A
<b>Rating Plug Range:</b>	0.4A to 1A