


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
PGL36120CU44A


by Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: For Use With: Approvals: Mounting Type: Terminal Type: Wire Size: Weight: Depth: Height: Width:	Provides overload and short circuit protection Panelboards and Switchboards UL Listed - CSA Certified - IEC Rated Unit Mount Lugs (ON and OFF ends) #3/0-500 AWG/kcmil(Al/Cu) 32 Pounds 8.07 Inches 16.26 Inches 8.27 Inches
---	---

Specification:

Description: Number of Poles: Sensor Rating: Voltage Rating: Interrupting Rating: Circuit Breaker Rating: Electronic Trip Unit: Trip Function: Installed Rating Plug: Rating Plug Range:	PowerPact P-frame Electronic Trip Circuit Breaker 3-Pole 1200A 600VAC 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC 100% Rated Micrologic Ammeter Trip Unit (6.0A) LSIG Type A 0.4A to 1A
---	---