



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
PGL36120U74AE1

SQUARE D
 by **Schneider Electric**
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

| | |
|----------------------|--|
| General Application: | Provides overload and short circuit protection |
| For Use With: | Panelboards and Switchboards |
| Approvals: | UL Listed - CSA Certified - IEC Rated |
| Mounting Type: | Unit Mount |
| Terminal Type: | Lugs (ON and OFF ends) |
| Wire Size: | #3/0-500 AWG/kcmil(Al/Cu) |
| Weight: | 32 Pounds |
| Depth: | 8.07 Inches |
| Height: | 16.26 Inches |
| Width: | 8.27 Inches |

Specification:

| | |
|-------------------------|---|
| Description: | PowerPact P-frame Electronic Trip Circuit Breaker |
| Number of Poles: | 3-Pole |
| Sensor Rating: | 1200A |
| Voltage Rating: | 600VAC |
| Interrupting Rating: | 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC |
| Circuit Breaker Rating: | 80% Rated |
| Electronic Trip Unit: | Micrologic Harmonic Trip Unit (6.0H) |
| Trip Function: | LSIG |
| Installed Rating Plug: | Type A |
| Rating Plug Range: | 0.4A to 1A |