



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

PJL36060CU33A



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
For Use With: Panelboards and Switchboards
Approvals: UL Listed - CSA Certified - IEC Rated
Mounting Type: Unit Mount
Terminal Type: Lugs (ON and OFF ends)
Wire Size: #3/0-500 AWG/kcmil(Al/Cu)
Weight: 32 Pounds
Depth: 8.07 Inches
Height: 12.86 Inches
Width: 8.27 Inches

Specification:

Description: PowerPact P-frame Electronic Trip Circuit Breaker
Number of Poles: 3-Pole
Sensor Rating: 600A
Voltage Rating: 600VAC
Interrupting Rating: 100kA at 240VAC - 65kA at 480VAC - 25kA at 600VAC
Circuit Breaker Rating: 100% Rated
Electronic Trip Unit: Micrologic Standard Trip Unit (5.0)
Trip Function: LSI
Installed Rating Plug: Type A
Rating Plug Range: 0.4A to 1A