



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
PKL36120U33A

SQUARE D
 by **Schneider Electric**
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 General Application: Provides overload and short circuit protection
 For Use With: Panelboards and Switchboards
 Approvals: UL Listed - CSA Certified - IEC Rated
 Mounting Type: Unit Mount
 Terminal Type: Lugs (ON and OFF ends)
 Wire Size: #3/0-500 AWG/kcmil(Al/Cu)
 Weight:
 Depth: 8.07 Inches
 Height: 16.26 Inches
 Width: 8.27 Inches

Specification:
 Description: PowerPact P-frame Electronic Trip Circuit Breaker
 Number of Poles: 3-Pole
 Sensor Rating: 1200A
 Voltage Rating: 600VAC
 Interrupting Rating: 65kA at 240VAC - 50kA at 480/600VAC
 Circuit Breaker Rating: 80% Rated
 Electronic Trip Unit: Micrologic Standard Trip Unit (5.0)
 Trip Function: LSI
 Installed Rating Plug: Type A
 Rating Plug Range: 0.4A to 1A