



AMPERE RATING	BYPASS TYPE	MAXIMUM SYSTEM VOLTAGE	SHORT CIRCUIT RATING	CATALOG NUMBER	SERIES	LINE SIDE PHASE AND NEUTRAL LUGS AWG/KCMIL
200	LEVER	120/240 VAC 1Ø 3W OR 208Y/120V (FROM A 3Ø 4W SYSTEM)	10K	RCM200SL	M02	#6-350 CU/AL

- NOTES:
- 1) 200 AMPS, 1 PHASE, 120/240 VAC 10KAIC
 - 2) PAINT- GRAY
 - 3) LOAD TERMINALS ARE RATED FOR 60° C. OR 75° C. CONDUCTOR.
 - 4) USE ONLY SQUARE D TYPE QOM2 (200A MAX).
 - 5) UNIT SHIPPED WITH FULL DEADFRONT OVER LOAD COMPARTMENT.

COMBINATION SERVICE ENTRANCE DEVICES
RINGLESS TYPE METER MAIN
RAINPROOF TYPE 3R ENCLOSURE
SURFACE MOUNT LEVER BYPASS



DWG# PWFDS-SYRS-0009
NO.