

Product data sheet

Characteristics

PZ42IZ-GR

Ficha de Alimentação de UPS da APC, IEC de bloqueio C14 PARA 4 tomadas de contacto de segurança (Schutzkontakt) (CEE 7/3), 230V Alemanha



Price*: 26.33 EUR



Visão geral

Prazo de entrega	Expedição normal num prazo máximo de 4 semanas
------------------	--

Geral

Equipamento fornecido	Manual do utilizador
-----------------------	----------------------

Físico

Cor	Preto
Profundidade	28,5 Cm
Altura	4 Cm
Peso net	0,36 Kg
Largura	4,468 Cm

Entrada

Frequência da rede	50/60 Hz
Potência de entrada	2500 W
Capacidade de corrente de comutação	10 A
Corrente máxima de entrada por fase	10 A
Plug standard	IEC 60320 C14 locking plug

Saída

Número de tomadas de corrente de energia	4
Norma da tomada	Schuko CEE 7

Conformidades

Certificações do produto	CE
--------------------------	----

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Ambiental

Temperatura do ar ambiente para a operação	0...45 °C
Altitude de funcionamento	0...10000 ft
Humidade relativa	0...95 % não-condensação
Temperatura ambiente para armazenamento	-40...70 °C
Altitude de armazenamento	0,00...15240,00 M
Humidade relativa de armazenamento	0...95 %

Unidades de embalagem

Peso da embalagem (Lbs)	0,45 Kg
Pacote 1 Altura	4,8 Cm
Pacote 1 largura	13 Cm
Pacote 1 Comprimento	31 Cm
SCC14	10731304336263
Número de unidades no pacote 2	6
Peso do pacote 2	2,93 Kg
Pacote 2 Altura	279,40 Mm
Largura do pacote 2	152,40 Mm
Comprimento do pacote 2	330,20 Mm
Número de unidades no pacote 3	378

Sustentabilidade da oferta

Diretiva RoHS da UE Conforme  Declaração RoHS Da EU

Garantia contractual

Garantia Reparar ou substituir 5 anos

Product Life Status : **Comercializado**