


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

RE22R1HMR



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Max. Switching Current: 8A
 Max. Switching Voltage: 250 V
 Max. Power Consumption: 3VA (AC), 1.5W (DC)
 Input Signals: Y1 - Control Signal
 Function Available: H, Hw
 Function Description: Interval relay
 Time Ranges: 0.05 s to 300 h
 Type of Output: Relay
 Contact Configuration: SPDT

Description: Timer, 24-240 VAC/VDC Input, 8A SPDT Relay Output, Interval
 Ambient Storage Temp.: -40 to +70 °C (-40 to +158 °F)
 Ambient Operating Temp.: -20 to +60 °C (-4 to +140 °F)
 Degree of Protection Term. Block: IP20
 Degree of Protection Housing: IP40
 Electrical Life @ Rated Load: 100,000 cycles
 Mechanical Life @ Rated Load: 20,000,000 cycles
 Dial Settings: Range = 1s to 300h, Time setting = 1 to 10
 Mounting: 35 mm DIN Rail