



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

RGA36100CU33A



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
For Use With: I-Line Panelboards and Switchboards
Approvals: UL Listed - CSA Certified - IEC Rated
Mounting Type: I-Line Plug-On
Terminal Type: I-Line Connection (ON end) - Lugs (OFF end)
Wire Size: (4) 3/0 through 600 kcmil Al or Cu
Weight:
Depth:
Height:
Width:
Mounting Height:

Specification:

Description: PowerPact R-frame Molded Case Circuit Breaker
Number of Poles: 3-Pole
Ampere Rating: 1000A
Voltage Rating: 600VAC
Interrupting Rating: 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC
Circuit Breaker Rating: 100% Rated
Fixed AC Magnetic Trip: