



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**RGA36120CU44A**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

**General Application:** Provides overload and short circuit protection  
**For Use With:** I-Line Panelboards and Switchboards  
**Approvals:** UL Listed - CSA Certified - IEC Rated  
**Mounting Type:** I-Line Plug-On  
**Terminal Type:** I-Line Connection (ON end) - Lugs (OFF end)  
**Wire Size:** (4) 3/0 through 600 kcmil Al or Cu  
**Weight:**  
**Depth:**  
**Height:**  
**Width:**  
**Mounting Height:**

**Specification:**

**Description:** PowerPact R-frame Molded Case Circuit Breaker  
**Number of Poles:** 3-Pole  
**Ampere Rating:** 1200A  
**Voltage Rating:** 600VAC  
**Interrupting Rating:** 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC  
**Circuit Breaker Rating:** 100% Rated  
**Fixed AC Magnetic Trip:**