



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**RKA36120CU41A**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection  
 For Use With: I-Line Panelboards and Switchboards  
 Approvals: UL Listed - CSA Certified - IEC Rated  
 Mounting Type: I-Line Plug-On  
 Terminal Type: I-Line Connection (ON end) - Lugs (OFF end)  
 Wire Size: (4) 3/0 through 600 kcmil Al or Cu  
 Weight:  
 Depth:  
 Height:  
 Width:  
 Mounting Height:

Specification:

Description: PowerPact R-frame Molded Case Circuit Breaker  
 Number of Poles: 3-Pole  
 Ampere Rating: 1200A  
 Voltage Rating: 600VAC  
 Interrupting Rating: 65kA at 240VAC - 65kA at 480VAC - 65kA at 600VAC  
 Circuit Breaker Rating: 100% Rated  
 Fixed AC Magnetic Trip: