



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

RKF36080CU31A

Technical Information:

General Application:	Provides overload and short circuit protection
For Use With:	Industrial Enclosures and Switchboards
Approvals:	UL Listed - CSA Certified - IEC Rated
Mounting Type:	Unit Mount
Terminal Type:	Bus Connection - Line: terminal - Load: terminal
Wire Size:	
Weight:	52
Depth:	14.49
Height:	16.24
Width:	16.53
Mounting Height:	

Description:	PowerPact R-frame Molded Case Circuit Breaker
Number of Poles:	3-Pole
Ampere Rating:	800A
Voltage Rating:	600VAC
Interrupting Rating:	65kA at 240VAC - 65kA at 480VAC - 65kA at 600VAC
Circuit Breaker Rating:	100% Rated
Fixed AC Magnetic Trip:	

Specification: