



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Note:  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**RKF36250U64AE1**

Technical Information:  
 General Application: Provides overload and short circuit protection  
 For Use With: Industrial Enclosures and Switchboards  
 Approvals: UL Listed - CSA Certified - IEC Rated  
 Mounting Type: Unit Mount  
 Terminal Type: Bus Connection - Line: terminal - Load: terminal  
 Wire Size:  
 Weight: 52  
 Depth: 14.49  
 Height: 16.24  
 Width: 16.53  
 Mounting Height:

Description:  
 Number of Poles: 3-Pole  
 Ampere Rating: 2500A  
 Voltage Rating: 600VAC  
 Interrupting Rating: 65kA at 240VAC - 65kA at 480VAC - 65kA at 600VAC  
 Circuit Breaker Rating: 80% Rated  
 Fixed AC Magnetic Trip:

Specification: