



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

RLA36100CU74AE1



Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone: +1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
 For Use With: I-Line Panelboards and Switchboards
 Approvals: UL Listed - CSA Certified - IEC Rated
 Mounting Type: I-Line Plug-On
 Terminal Type: I-Line Connection (ON end) - Lugs (OFF end)
 Wire Size: (4) 3/0 through 600 kcmil Al or Cu
 Weight:
 Depth:
 Height:
 Width:
 Mounting Height:

Specification:

Description: PowerPact R-frame Molded Case Circuit Breaker
 Number of Poles: 3-Pole
 Ampere Rating: 1000A
 Voltage Rating: 600VAC
 Interrupting Rating: 125kA at 240VAC - 100kA at 480VAC - 50kA at 600VAC
 Circuit Breaker Rating: 100% Rated
 Fixed AC Magnetic Trip: