



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
RLF36250

Technical Information:
 General Application: Provides overload and short circuit protection
 For Use With: Industrial Enclosures and Switchboards
 Approvals: UL Listed - CSA Certified - IEC Rated
 Mounting Type: Unit Mount
 Terminal Type: Bus Connection - Line: terminal - Load: terminal
 Wire Size:
 Weight: 52
 Depth: 14.49
 Height: 16.24
 Width: 16.53
 Mounting Height:

Description:
 Number of Poles: 3-Pole
 Ampere Rating: 2500A
 Voltage Rating: 600VAC
 Interrupting Rating: 125kA at 240VAC - 100kA at 480VAC - 50kA at 600VAC
 Circuit Breaker Rating: 80% Rated
 Fixed AC Magnetic Trip:

Specification:
 PowerPact R-frame Molded Case Circuit Breaker