

SBPSU10K20HC1M1-WP

Quadro de Bypass de Manutenção Smart-UPS VT da APC 10-20kVA 400V para Montagem na Parede



Visão geral

Prazo de entrega	Expedição normal num prazo máximo de 4 semanas
------------------	--

Principal

Tensão de entrada	400 V trifásico
Output voltage	400 V trifásico
Número de cabos	1
Equipamento fornecido	Manual de instalação Manual do utilizador

Físico

Cor	Preto
Altura	31,5 Cm
Largura	30,5 Cm
Profundidade	17,5 Cm
Peso líquido	7,01 Kg
Local de montagem	Frontal
Mounting preference	No preference
Modo de montagem	Not rack-mountable

Entrada

Frequência da rede	50 Hz +/- 3 Hz
--------------------	----------------

Conformidade

Normas	EN 50091-2 EN/IEC 62040-3 EN/IEC 62040-1-1
--------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ambiental

Temperatura do ar ambiente para operação	0...40 °C
Humidade relativa	0...95 %
Altitude de funcionamento	0...50000 ft
Temperatura do ar ambiente para armazenamento	0...40 °C
Armazenamento Humidade relativa	0...95 %
Altitude de armazenamento	0,0000000000...15240,0000000000 M

Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	44,2 Cm
Package 1 Width	25,4 Cm
Package 1 Length	38,1 Cm
Package 1 Weight	7,73 Kg
Number of Units in Package 3	1

Garantia contratual

Garantia	1 ano (apenas peças)
----------	----------------------

Product Life Status : **Comercializado**