



Overview

| | |
|--------------|---|
| Presentation | EASY UPS Line Interactive is an Uninterruptable Power Supply designed for essential power protection in the most unstable power conditions. |
| Lead time | Usually in Stock |

Main

| | |
|---------------------------|--|
| Main Input Voltage | 230 V |
| Input voltage | 220 V 240 V |
| Output voltage | 230 V |
| Rated power in W | 2100 W |
| Rated power in VA | 3000 VA |
| Product or component type | Uninterruptible power supply (UPS) |
| Input Connection Type | IEC 60320 C20 |
| Output connection type | 6 IEC 60320 C13 |
| Number of cables | 1 |
| Battery type | Lead-acid battery |
| Provided equipment | Documentation CD User manual USB cable |

Batteries & Runtime

| | |
|--------------------------------|---------------|
| Number of battery filled slots | 0 |
| Number of battery free slots | 0 |
| Battery recharge time | 4 H |
| Battery voltage | 48 V |
| Battery capacity | 9 Ah |
| Battery charger power | 99 W rated |
| Battery life | 3...5 Year(S) |
| Extended runtime | 0 |

General

| | |
|-------------------------------------|----|
| Number of power module free slots | 0 |
| Number of power module filled slots | 0 |
| Redundant | No |
| UPS size | WS |

Physical

| | |
|---------------------|--------------------|
| Colour | Black |
| Height | 24 Cm |
| Width | 18 Cm |
| Depth | 45.5 Cm |
| Net weight | 25.2 Kg |
| Mounting preference | No preference |
| Mounting mode | Not rack-mountable |
| Two post mountable | 0 |
| USB compatible | No |

Input

| | |
|----------------------|----------------------------------|
| Network frequency | 45...65 Hz +/- 1 Hz auto-sensing |
| Input voltage limits | 165...295 V |

Output

| | |
|----------------------------------|----------------------------------|
| Maximum configurable power in W | 2100 W |
| Output frequency | 50/60 Hz +/- 1 Hz unsynchronised |
| Crest factor | 3 : 1 |
| UPS type | Line interactive |
| Wave type | Sine wave |
| Graph display | 1 |
| Maximum configurable power in VA | 3000 VA |
| Transfer time | 2-6 ms typical : 12 ms maximum |

Conformance

| | |
|------------------------|--|
| Product certifications | CE[RETURN]UKCA |
| Standards | EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018 |

Environmental

| | |
|---------------------------------------|-------------------------|
| Ambient air temperature for operation | 0...40 °C |
| Relative humidity | 0...95 % non-condensing |
| Operating altitude | 0...3000 m |
| Ambient air temperature for storage | -10...40 °C |
| Storage Relative Humidity | 0...95 % non-condensing |
| Storage altitude | 0...15000 M |
| Acoustic level | 45 dBA |
| IP degree of protection | IP20 |

Communications & Management

| | |
|------------|--|
| Free slots | 1 |
| Alarm | Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm |

Surge Protection and Filtering

| | |
|-------------------|-------|
| Surge energy rate | 125 J |
|-------------------|-------|

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 32.000 Cm |
| Package 1 Width | 41.000 Cm |
| Package 1 Length | 60.000 Cm |
| Package 1 Weight | 29.280 Kg |
| Unit Type of Package 2 | P12 |
| Number of Units in Package 2 | 4 |
| Package 2 Height | 45.000 Cm |
| Package 2 Width | 80.000 Cm |
| Package 2 Length | 120.000 Cm |
| Package 2 Weight | 129.120 Kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Product Life Status : **Commercialised**