

Product data sheet

Characteristics

SMVS750CAI

Easy UPS 1 Ph Line Interactive, 750VA,
Tower, 230V, 6x IEC C13 outlets, AVR,
Intelligent Card Slot + Dry Contact, LCD



Overview

Presentation	EASY UPS Line Interactive is an Uninterruptable Power Supply designed for essential power protection in the most unstable power conditions.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Input voltage	220 V 240 V
Output voltage	230 V
Rated power in W	525 W
Rated power in VA	750 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 60320 C14
Output connection type	6 IEC 60320 C13
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	Documentation CD User manual USB cable

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 H
Battery voltage	24 V
Battery capacity	7 Ah
Battery charger power	33 W rated
Battery life	3...5 Year(S)
Extended runtime	0

General

Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS

Physical

Colour	Black
Height	22 Cm
Width	16 Cm
Depth	41 Cm
Net weight	13.6 Kg
Mounting support	Floor-standing
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Network frequency	45...65 Hz +/- 1 Hz auto-sensing
Input voltage limits	165...290 V

Output

Maximum configurable power in W	525 W
Output frequency	50/60 Hz +/- 1 Hz unsynchronised
Crest factor	3 : 1
UPS type	Line interactive
Wave type	Sine wave
Graph display	1
Maximum configurable power in VA	750 VA
Transfer time	2-6 ms typical : 12 ms maximum

Conformance

Product certifications	CE[RETURN]UKCA
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-10...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...15000 M
Acoustic level	45 dBA
IP degree of protection	IP20

Communications & Management

Free slots	1
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm

Surge Protection and Filtering

Surge energy rate	190 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	27.200 Cm
Package 1 Width	33.500 Cm
Package 1 Length	50.800 Cm
Package 1 Weight	16.601 Kg
Unit Type of Package 2	P12
Number of Units in Package 2	4
Package 2 Height	45.000 Cm
Package 2 Width	80.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	81.004 Kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**