



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Rack mounting brackets User manual Warranty card
--------------------	--------------------------------------------------------

Physical

Colour	Black
Depth	59.4 Cm
Height	8.5 Cm
Product weight	40.6 Kg
Number of rack unit	2U
Width	43.2 Cm

Conformance

Standards	OSHPD
-----------	-------

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Storage Relative Humidity	Non-condensing 0...95 %

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Battery voltage	96 V
Battery type	Lead-acid battery
Number of battery replacement quantity	2

Packing Units

Package 1 Weight	44.5 Kg
Package 1 Height	23.9 Cm
Package 1 width	59.9 Cm
Package 1 Length	83.1 Cm
Number of Units in Package 3	6

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**