



Overview

Model Name	APC Easy UPS On-Line SRV RM 2000 VA 230V with Rail Kit
Includes	CD with software , Rack Mounting support rails , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Albania , Andorra , Argentina , Armenia , Austria , Belarus , Belgium , Bosnia And Herzegovina , Brazil , Bulgaria , Croatia , Cyprus , Czech Republic , Denmark , Estonia , Finland , France , Germany , Gibraltar , Greece , Hungary , Iceland , Ireland , Israel , Italy , Kazakhstan , Latvia , Liechtenstein , Lithuania , Macedonia , Malta , Moldova , Republic Of , Netherlands , Norway , Paraguay , Poland , Romania , Russian Federation , Slovakia (Slovak Republic) , Slovenia , Spain , Sweden , Switzerland , Ukraine , Uruguay

Output

Output Power Capacity	1600 Watts / 2000 VA
Max Configurable Power (Watts)	1600 Watts / 2000 VA
Nominal Output Voltage	230V
Output Voltage Distortion	3%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	220, 240V
Waveform Type	Sine wave

Input

Nominal Input Voltage	230V
Input Frequency	40 - 70 Hz
Input Connections	IEC-320 C14
Input voltage range for main operations	160 - 280 V
Other Input Voltages	220 , 240

Communications & Management

Control panel	Multi-function LCD status and control console
---------------	-----------------------------------------------

Surge Protection and Filtering

Surge energy rating	600 joules
---------------------	------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Physical

Maximum Height	86.0 mm
Maximum Width	437.0 mm
Maximum Depth	462.0 mm
Net Weight	18.2 kg
Shipping Weight	20.7 kg
Shipping Height	142.0 mm
Shipping Width	551.0 mm
Shipping Depth	599.0 mm

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-20 - 50 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-14763.6 meters
Audible noise at 1 meter from surface of unit	0.000 dB

Conformance

Approvals	CE , IEC 62040-1-1 , IEC 62040-1-2
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs
REACH SVHC	Lead, CAS#7439-92-1 30% , SVHC-191