



### Overview

Model Name	APC Easy UPS On-Line SRV RM 3000 VA 230V with Rail Kit
Includes	CD with software , Rack Mounting support rails , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Armenia , Austria , Azerbaijan , Belarus , Belgium , Benin , Bosnia And Herzegovina , Botswana , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Central African Republic , Chad , Chile , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Croatia , Cyprus , Czech Republic , Denmark , Egypt , Estonia , Finland , France , Georgia , Gibraltar , Greece , Guadeloupe , Guinea , Hungary , Iceland , Indonesia , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , KOREA, REPUBLIC OF , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Malta , Martinique , Mauritania , Mauritius , Moldova , Republic Of , Mongolia , Morocco , Myanmar , Namibia , Netherlands , Niger , Norway , Pakistan , Peru , Philippines , Poland , Portugal , Romania , Russian Federation , SAINT LUCIA , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Spain , Sweden , Switzerland , Tajikistan , Thailand , Togo , Tunisia , Turkmenistan , Ukraine , Uruguay , Uzbekistan , Viet Nam , Western Sahara , Zambia , Zimbabwe

### Output

Output Power Capacity	2400 Watts / 3000 VA
Max Configurable Power (Watts)	2400 Watts / 3000 VA
Nominal Output Voltage	230V
Output Voltage Distortion	0%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	220, 240V
	Double Conversion Online
Waveform Type	Sine wave

### Input

Nominal Input Voltage	230V
Input Frequency	40 - 70 Hz
Input Connections	IEC-320 C20
Input voltage range for main operations	160 - 280 V
Other Input Voltages	220 , 240

### Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm

## Surge Protection and Filtering

Surge energy rating	600 joules
---------------------	------------

## Physical

Maximum Height	86.0 mm
Maximum Width	437.0 mm
Maximum Depth	632.0 mm
Net Weight	27.6 kg
Shipping Weight	29.0 kg
Shipping Height	229.0 mm
Shipping Width	569.0 mm
Shipping Depth	795.0 mm

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-20 - 50 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-14763.6 meters
Audible noise at 1 meter from surface of unit	0.000 dB

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs
REACH SVHC	Lead, CAS#7439-92-1 30% , SVHC-191