



### Overview

Model Name	APC Easy UPS SRV 6000VA 230V
Includes	CD with software , USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Armenia , Austria , Azerbaijan , Belarus , Belgium , Benin , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Cambodia , Cameroon , Central African Republic , Chad , Chile , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Croatia , Cyprus , Czech Republic , Denmark , Dominica , East Timor , Egypt , Estonia , Finland , France , Gabon , Gambia , Georgia , Germany , Gibraltar , Greece , Guadeloupe , Guinea , French Guiana , Hong Kong , Hungary , Indonesia , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , KOREA, REPUBLIC OF , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Malta , Martinique , Mauritania , Mauritius , Moldova , Republic Of , Mongolia , Morocco , Myanmar , Namibia , Netherlands , Netherlands Antilles , Niger , Norway , Pakistan , Paraguay , Peru , Philippines , Poland , Portugal , Romania , Russian Federation , SAINT LUCIA , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , South Africa , Spain , Sweden , Switzerland , Tajikistan , Thailand , Togo , Tunisia , Turkey , Turkmenistan , Ukraine , Uruguay , Uzbekistan , Viet Nam , Western Sahara , Zambia , Zimbabwe

### Output

Output Power Capacity	6000 Watts / 6000 VA
Max Configurable Power (Watts)	6000 Watts / 6000 VA
Nominal Output Voltage	230V
Other Output Voltages	220, 240V
Crest Factor	3 : 1
	Double Conversion Online
Waveform Type	Sine wave

### Input

Nominal Input Voltage	230V
Input Frequency	40 - 70 Hz
Input Connections	Hard Wire 3-wire
Other Input Voltages	220 , 240

### Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)

## Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	600 joules
---------------------	------------

## Physical

Maximum Height	685.0 mm
Maximum Width	190.0 mm
Maximum Depth	374.0 mm
Net Weight	54.0 kg
Shipping Weight	66.0 kg
Shipping Height	910.0 mm
Shipping Width	290.0 mm
Shipping Depth	495.0 mm

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-3000 meters
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-14763.6 meters
Audible noise at 1 meter from surface of unit	0.000 dB

## Conformance

Approvals	CE , IEC 62040-1-1 , IEC 62040-1-2
Standard warranty	2 years repair or replace

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs