



### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Product or component type	Uninterruptible power supply (UPS)
Number of rack unit	2U
Battery type	Lead-acid battery
Provided equipment	User manual Battery cable Rack mounting brackets

### Batteries & Runtime

Number of battery blocks per string	3
Device mounting	Rack mount
Number of battery filled slots	0
Number of battery free slots	0
Battery voltage	36 V

### Physical

Colour	Black
Height	8.6 Cm
Width	43.8 Cm
Depth	41.2 Cm
Net weight	21 Kg
Mounting mode	Rack-mounted with kit

### Conformance

Product certifications	CE[RETURN]UKCA[RETURN]EAC[RETURN]EN/IEC 62040-1
------------------------	---

### Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...15000 M

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 Cm
Package 1 Width	50 Cm
Package 1 Length	60 Cm
Package 1 Weight	24.149 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	16
Package 2 Height	108.6 Cm
Package 2 Width	100 Cm
Package 2 Length	120 Cm
Package 2 Weight	427.4 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**