



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
T02AN13G7

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 Max. Continuous Current Rating: 600V / 9A
 Certifications: UL Listed, CSA, CE
 RoHS: Yes
 Termination Method: Screw Clamp
 Weight (lbs): 0.91
 Power Wire Size (AWG): #8 - #18
 Control Wire Size (AWG): #10 - #18
 Mounting: 35mm DIN Rail, Panel

Specification:
 Description: TeSys N Contactor Sz00 3P 120VAC
 Type: FVNR
 Voltages Code: G7 at 120VAC
 Coil Consumption: Inrush 70 VA
 Sealed 7 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
1/3 HP	1 HP	1.5 HP	1.5 HP	2 HP	2 HP