


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**T02BN23T7**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Max. Continuous Current Rating: 600V / 18A  
 Certifications: UL Listed, CSA, CE  
 RoHS: Yes  
 Termination Method: Screw Clamp  
 Weight (lbs): 2.08  
 Power Wire Size (AWG): #8 - #18  
 Control Wire Size (AWG): #10 - #18  
 Mounting: 35mm DIN Rail, Panel

**Specification:**

Description: TeSys N Rev. Contactor Sz0 3P 480VAC  
 Type: FVR  
 Voltages Code: T7 at 480Vac

Coil Consumption: Inrush 70 VA  
 Sealed 7 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
1 HP	2 HP	3 HP	3 HP	5 HP	5 HP