

Product data sheet

Characteristics

VLS1GD1

Disconnect switch, TeSys VLS, additional earthing ground terminal, for 16A to 40A, size 1 (36mm), door mount

Product availability: Stock - Normally stocked in distribution facility



Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Range	TeSys
Device short name	VLS1G
Product or Component Type	Additional earthing block
Performance level	High performance
Contacts type and composition	Without
Range compatibility	TeSys TeSys VARIO LS VLS3P TeSys TeSys VARIO LS VLS1P TeSys TeSys VARIO LS VLSA
Network type	AC
Network Frequency	50/60 Hz

Complementary

Mounting Location	Right Left
Mounting Support	Door
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 KV
[Ith] conventional free air thermal current	63 A (at 131 °F (55 °C))
[Ithe] conventional enclosed thermal current	63 A
Connections - terminals	Screw clamp terminals 0.02 in ² (10 mm ²) solid screw clamp terminals 0.02 in ² (16 mm ²) flexible - without cable end
Tightening torque	15.93...17.70 Lbf.In (1.8...2 N.m) screw clamp terminals
Height	3.07 In (78 mm)
Width	0.47 In (12 mm)
Depth	1.72 In (43.6 mm)
Net Weight	0.09 Lb(US) (0.04 kg)
Color	Gray

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3
Product Certifications	cULus[RETURN]GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-11

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156839
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 In (3.3 cm)
Package 1 Width	3.50 In (8.89 cm)
Package 1 Length	3.00 In (7.62 cm)
Package 1 Weight	0.09 Lb(US) (0.04 kg)
Unit Type of Package 2	S01
Number of Units in Package 2	30
Package 2 Height	5.91 In (15 cm)
Package 2 Width	5.91 In (15 cm)
Package 2 Length	15.75 In (40 cm)
Package 2 Weight	3.21 Lb(US) (1.455 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status : **End of commercialisation**