

# VLS1GR1

Disconnect switch, TeSys VLS, additional earthing ground terminal, for 16A to 63A, size 1 (36mm), DIN mount

Product availability: Stock - Normally stocked in distribution facility



## Commercial status

This Product is Obsolete :

 This Product is Obsolete

## Main

Range	TeSys
Device short name	VLS1G
Product or Component Type	Additional earthing block
Performance level	High performance
Contacts type and composition	Without
Range compatibility	TeSys TeSys VARIO LS VLS3P[RETURN]TeSys TeSys VARIO LS VLS1P[RETURN]TeSys TeSys VARIO LS VL5A
Network type	AC
Network Frequency	50/60 Hz

## Complementary

Mounting Location	Left Right
Mounting Support	DIN rail
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 KV
[Ith] conventional free air thermal current	63 A (at 131 °F (55 °C))
[Ithe] conventional enclosed thermal current	63 A
Connections - terminals	Screw clamp terminals 0.02 in <sup>2</sup> (10 mm <sup>2</sup> ) solid screw clamp terminals 0.02 in <sup>2</sup> (16 mm <sup>2</sup> ) flexible - without cable end
Tightening torque	15.93...17.70 Lbf.In (1.8...2 N.m) screw clamp terminals
Height	3.07 In (78 mm)
Width	0.47 In (12 mm)
Depth	1.72 In (43.6 mm)
Net Weight	0.09 Lb(US) (0.04 kg)
Color	Gray

## Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3
Product Certifications	cULus[RETURN]GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-11

## Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156815
Returnability	No
Country of origin	IT

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 In (3.3 cm)
Package 1 Width	3.50 In (8.89 cm)
Package 1 Length	3.00 In (7.62 cm)
Package 1 Weight	0.09 Lb(US) (0.04 kg)
Unit Type of Package 2	S01
Number of Units in Package 2	30
Package 2 Height	5.91 In (15 cm)
Package 2 Width	5.91 In (15 cm)
Package 2 Length	15.75 In (40 cm)
Package 2 Weight	3.08 Lb(US) (1.395 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

Product Life Status : **End of commercialisation**