

Product data sheet

Characteristics

VLS1P040D1S

Disconnect switch, TeSys VLS, additional pole, 40A, for 16A to 40A switch, size 1, door mount

Product availability: Stock - Normally stocked in distribution facility

Price*: 26.72 USD



Main

| | |
|-------------------------------|----------------------------|
| Range | TeSys |
| Device short name | VLS1P |
| Product or Component Type | Additional pole |
| Performance level | High performance |
| Poles description | 1P |
| Contacts type and composition | 1 NO |
| Contact operation | Simultaneous |
| Range compatibility | TeSys TeSys VARIO LS VLS3P |
| Network type | AC |
| Network Frequency | 50/60 Hz |
| Suitability for isolation | Yes |

Complementary

| | |
|--|--|
| Mounting Location | Right Left |
| Mounting Support | Door |
| [Ue] rated operational voltage | 690 V AC 50/60 Hz |
| [Uimp] rated impulse withstand voltage | 8 KV |
| [Ith] conventional free air thermal current | 40 A (at 131 °F (55 °C)) |
| [Ithe] conventional enclosed thermal current | 40 A |
| [Ie] rated operational current | 40 A Ue: 600 V UL 508 40 A AC-21A Ue: 400 V 40 A AC-21A Ue: 500 V 40 A AC-21A Ue: 690 V 40 A AC-22A Ue: 400 V 40 A AC-22A Ue: 500 V 40 A AC-22A Ue: 690 V 40 A AC-23A Ue: 400 V 25 A AC-23A Ue: 500 V 25 A AC-23A Ue: 690 V |
| Rated operational power in W | 18.5 KW 400 V AC-23A) 18.5 KW 500 V AC-23A) 22 KW 690 V AC-23A) |
| Intermittent duty class | Class 120 - 60 % |

| | |
|---|---|
| Making capacity | 60 A 690 V AC-21A 120 A 690 V AC-22A 400 A 690 V AC-23A |
| [Icm] rated short-circuit making capacity | 1128 A 690 V |
| [Icw] rated short-time withstand current | 800 A 690 V 1 s |
| Rated conditional short-circuit current | 50 KA 400 V 40 A gG |
| Breaking capacity | 60 A 690 V AC-21A) 120 A 690 V AC-22A) 320 A 690 V AC-23A) |
| Mechanical durability | 100000 Cycles |
| Electrical durability | 100000 Cycles AC-21A |
| Connections - terminals | Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.02 in ² (16 mm ²) flexible - without cable end |
| Tightening torque | Power circuit 15.93...17.70 lbf.in (1.8...2 N.m) screw clamp terminals |
| Height | 3.07 In (78 mm) |
| Width | 0.47 In (12 mm) |
| Depth | 1.72 In (43.6 mm) |
| Net Weight | 0.09 Lb(US) (0.04 kg) |
| Color | Gray |

Environment

| | |
|---------------------------------------|--|
| Standards | UL 508 CSA C22.2 No 14 IEC 60947-3 |
| Product Certifications | cULus[RETURN]GL |
| IP degree of protection | IP20 conforming to IEC 60529 |
| Mechanical robustness | Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27 |
| Ambient air temperature for operation | -13...131 °F (-25...55 °C) |
| Fire resistance | 1760 °F (960 °C) IEC 60695-2-11 |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US10CP121734 |
| Discount Schedule | 0CP1 |
| GTIN | 3606481156648 |
| Returnability | Yes |
| Country of origin | IT |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.10 In (2.800 cm) |
| Package 1 Width | 2.64 In (6.700 cm) |
| Package 1 Length | 3.19 In (8.100 cm) |
| Package 1 Weight | 1.55 Oz (44.000 g) |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 30 |
| Package 2 Height | 5.91 In (15.000 cm) |
| Package 2 Width | 5.91 In (15.000 cm) |
| Package 2 Length | 15.75 In (40.000 cm) |
| Package 2 Weight | 3.32 Lb(US) (1.508 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |

Product Life Status : **Commercialised**