

Product data sheet

Characteristics

VLS8C2

Disconnect switch, TeSys VLS, interlock for line changeover (I-0-II), size 2, 30A to 125A devices

Product availability: Stock - Normally stocked in distribution facility

Price*: 124.80 USD



Main

Range	TeSys
Product or Component Type	Mechanical interlock
Accessory / separate part category	Interlocking accessory
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 padlock 0.16 in (4 mm)
Marking	1 - 0 - 2

Complementary

Fixing Mode	By clips and screws
Tightening torque	4.43 Lbf.In (0.5 N.m)
Height	1.77 In (45 mm)
Width	5.51 In (140 mm)
Depth	1.06 In (27 mm)
Net Weight	0.17 Lb(US) (0.075 kg)

Environment

Standards	UL98 CSA C22.2 No 4
Product Certifications	cULus[RETURN]EAC
IP Degree of Protection	IP20

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156860
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.95 In (7.500 cm)
Package 1 Width	2.17 In (5.500 cm)
Package 1 Length	5.71 In (14.500 cm)
Package 1 Weight	3.95 Oz (112.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	35
Package 2 Height	11.81 In (30.000 cm)
Package 2 Width	11.81 In (30.000 cm)
Package 2 Length	15.75 In (40.000 cm)
Package 2 Weight	9.71 Lb(US) (4.405 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status : **Commercialised**