

Product data sheet

Characteristics

VLS8M1

Disconnect switch, TeSys VLS, coupling system for 6 to 8 pole switch disconnectors, size 1, 16A to 40A devices

Product availability: Stock - Normally stocked in distribution facility

Price*: 51.37 USD



Main

Range	TeSys
Product or Component Type	Mechanical interlock
Accessory / separate part category	Coupling accessory
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 padlock 0.16 in (4 mm)
Marking	0 - 1

Complementary

Fixing Mode	By clips and screws
Tightening torque	4.43 Lbf.In (0.5 N.m)
Height	1.77 In (45 mm)
Width	2.83 In (72 mm)
Depth	1.06 In (27 mm)
Net Weight	0.11 Lb(US) (0.05 kg)

Environment

Standards	UL 508 CSA C22.2 No 14
Product Certifications	cULus[RETURN]EAC
IP Degree of Protection	IP20

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156877
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.85 In (4.7 cm)
Package 1 Width	2.56 In (6.5 cm)
Package 1 Length	3.58 In (9.1 cm)
Package 1 Weight	2.40 Oz (68.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	28
Package 2 Height	5.91 In (15.0 cm)
Package 2 Width	11.81 In (30.0 cm)
Package 2 Length	15.75 In (40.0 cm)
Package 2 Weight	5.20 Lb(US) (2.359 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status : **Commercialised**