

# Product data sheet

## Characteristics

# VLS8M2

Disconnect switch, TeSys VLS, coupling system for 6 to 8 pole switch disconnectors, size 2, 30A to 125A devices

Product availability: Stock - Normally stocked in distribution facility

Price\*: 63.36 USD



### Main

Range	TeSys
Product or Component Type	Mechanical interlock
Accessory / separate part category	Coupling accessory
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 padlock 0.16 in (4 mm)
Marking	0 - 1

### Complementary

Fixing Mode	By clips and screws
Tightening torque	4.43 Lbf.In (0.5 N.m)
Height	1.77 In (45 mm)
Width	5.51 In (140 mm)
Depth	1.06 In (27 mm)
Net Weight	0.17 Lb(US) (0.075 kg)

### Environment

Standards	UL98 CSA C22.2 No 4
Product Certifications	cULus[RETURN]EAC
IP Degree of Protection	IP20

### Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156884
Returnability	Yes
Country of origin	IT

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.95 In (7.500 cm)
Package 1 Width	2.09 In (5.300 cm)
Package 1 Length	5.71 In (14.500 cm)
Package 1 Weight	4.20 Oz (119.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	35
Package 2 Height	11.81 In (30.000 cm)
Package 2 Width	11.81 In (30.000 cm)
Package 2 Length	15.75 In (40.000 cm)
Package 2 Weight	10.23 Lb(US) (4.642 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

Product Life Status : **Commercialised**