

Product data sheet

Characteristics

VLSA11DS

Disconnect switch, TeSys VLS, auxiliary contact block, 1 normally closed and 1 normally open, door

Product availability: Stock - Normally stocked in distribution facility

Price*: 25.16 USD



Main

Range	TeSys
Device short name	VLSA
Product or Component Type	Auxiliary contact block
Performance level	High performance
Contacts type and composition	1 NC + 1 NO
Contact operation	Simultaneous 1 NC Simultaneous 1 NO
Range compatibility	TeSys TeSys VARIO LS VLSA[RETURN]TeSys TeSys VARIO LS VLS3P[RE- TURN]TeSys TeSys VARIO LS VLS1P
Network type	DC AC
Network Frequency	50/60 Hz

Complementary

Mounting Location	Right Left
Mounting Support	Door
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 KV
[Ith] conventional free air thermal current	10 A (at 131 °F (55 °C))
[Ithe] conventional enclosed thermal current	10 A
[Ie] rated operational current	6 A AC-15)24 V AC 6 A AC-15)48 V AC 6 A AC-15)127 V AC 3 A AC-15)240 V AC 3 A DC-13)24 V DC 1.5 A DC-13)48 V DC 0.55 A DC-13)127 V DC 0.27 A DC-13)240 V DC
Minimum output current	10 MA
Minimum output voltage	5 V
Connections - terminals	Control circuit screw clamp terminals 0.00 in ² (2.5 mm ²) flexible - without cable end
Tightening torque	Control circuit 7.08...8.85 lbf.in (0.8...1 N.m) screw clamp terminals

Height	2.86 In (72.6 mm)
Width	0.33 In (8.5 mm)
Depth	1.82 In (46.2 mm)
Net Weight	0.07 Lb(US) (0.03 kg)
Color	Gray

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3 IEC 60947-5
Product Certifications	cULus[RETURN]GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1562 °F (850 °C) IEC 60695-2-11

Ordering and shipping details

Category	US10CP121734
Discount Schedule	OCP1
GTIN	3606481156747
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.14 In (2.9 cm)
Package 1 Width	2.60 In (6.6 cm)
Package 1 Length	3.46 In (8.8 cm)
Package 1 Weight	1.34 Oz (38.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	30
Package 2 Height	5.91 In (15.0 cm)
Package 2 Width	5.91 In (15.0 cm)
Package 2 Length	15.75 In (40.0 cm)
Package 2 Weight	3.01 Lb(US) (1.365 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Product Life Status : **Commercialised**