

Product data sheet

Characteristics

VLSFH1UL

Disconnect switch, TeSys VLS, CC fuse holder, for 3 pole disconnect switch, for up to 25A fuse

Product availability: Stock - Normally stocked in distribution facility

Price*: 42.38 USD



Main

Range	TeSys
Product name	TeSys VARIO LS
Device short name	VLSFH
Fuse size	CC
Product or Component Type	Fuse holder
Poles description	3P
Network type	AC

Complementary

Network Frequency	50/60 Hz
Mounting Support	DIN rail
[Ui] rated insulation voltage	690 V AC 50/60 Hz
[Ith] conventional free air thermal current	25 A 131 °F (55 °C)
Connections - terminals	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.02 in ² (16 mm ²) flexible without cable end
Tightening torque	Power circuit 15.9...17.7 lbf.in (1.8...2 N.m) screw clamp terminals
Height	3.0 In (75.2 mm)
Width	2.07 In (52.5 mm)
Depth	3.2 In (80.1 mm)
Net Weight	0.298 Lb(US) (0.135 kg)

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3
Product Certifications	cULus[RETURN]GL
IP degree of protection	IP20 IEC 60529
Ambient air temperature for operation	-13.0000000000...131.0000000000 °F (-25...55 °C)

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481157140
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.559 In (6.500 cm)
Package 1 Width	3.543 In (9.000 cm)
Package 1 Length	3.819 In (9.700 cm)
Package 1 Weight	4.762 Oz (135.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Height	5.906 In (15.000 cm)
Package 2 Width	11.811 In (30.000 cm)
Package 2 Length	15.748 In (40.000 cm)
Package 2 Weight	6.054 Lb(US) (2.746 kg)

Offer Sustainability

RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status : **Commercialised**