

Product data sheet

Characteristics

VLSH1S5B

Disconnect switch, TeSys VLS, recessed rotary handle, screw mounting, 65x65 mm, black handle, 5 mm shaft

Product availability: Stock - Normally stocked in distribution facility

Price*: 42.81 USD



Main

Range	TeSys
Device short name	VLSH
Product or Component Type	Rotary handle
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1 OFF-ON

Complementary

Fixing mode	By 4 screws
Tightening torque	20.36 Lbf.In (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.56 In (65 mm)
Width	2.56 In (65 mm)
Depth	1.81 In (46 mm)
Net Weight	0.16 Lb(US) (0.072 kg)

Environment

IP Degree of Protection	IP65
NEMA degree of protection	NEMA 1 NEMA 12/3R NEMA 4 NEMA 4X

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156952
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.77 In (4.5 cm)
Package 1 Width	2.56 In (6.5 cm)
Package 1 Length	2.56 In (6.5 cm)
Package 1 Weight	2.26 Oz (64 g)
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	5.91 In (15 cm)
Package 2 Width	11.81 In (30 cm)
Package 2 Length	15.75 In (40 cm)
Package 2 Weight	60.85 Lb(US) (27.6 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status : **Commercialised**