

Product data sheet

Characteristics

VLSH2H5RD

Disconnect switch, TeSys VLS, protruding rotary handle, hole mounting, 65x65mm, red handle, 5mm shaft, defeatable

Product availability: Stock - Normally stocked in distribution facility

Price*: 61.89 USD



Main

Range	TeSys
Device short name	VLSH
Product or Component Type	Rotary handle
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1

Complementary

Fixing mode	Hole 0.89 in (22.5 mm)
Tightening torque	20.36 Lbf.In (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.56 In (65 mm)
Width	2.56 In (65 mm)
Depth	2.85 In (72.5 mm)
Net Weight	0.14 Lb(US) (0.064 kg)

Environment

IP Degree of Protection	IP65
NEMA degree of protection	NEMA 1 NEMA 2 UL 508 NEMA 3R UL 508 NEMA 4 UL 508 NEMA 4X UL 508 NEMA 12 UL 508 NEMA 12K UL 508

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156921
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 In (5.000 cm)
Package 1 Width	2.56 In (6.500 cm)
Package 1 Length	2.56 In (6.500 cm)
Package 1 Weight	2.19 Oz (62.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	5.91 In (15.000 cm)
Package 2 Width	11.81 In (30.000 cm)
Package 2 Length	15.75 In (40.000 cm)
Package 2 Weight	6.18 Lb(US) (2.805 kg)

Offer Sustainability

RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status : **Commercialised**