

# Product data sheet

## Characteristics

# VLSH2H5R

Disconnect switch, TeSys VLS, protruding rotary handle, hole mounting, 65x65mm, red handle, 5mm shaft

Product availability: Stock - Normally stocked in distribution facility

Price\*: 23.97 USD



### Main

Range	TeSys
Device short name	VLSH
Product or Component Type	Rotary handle
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1 OFF-ON

### Complementary

Fixing mode	Hole 0.89 in (22.5 mm)
Tightening torque	20.36 Lbf.In (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.56 In (65 mm)
Width	2.56 In (65 mm)
Depth	2.85 In (72.5 mm)
Net Weight	0.15 Lb(US) (0.068 kg)

### Environment

IP Degree of Protection	IP65
NEMA degree of protection	NEMA 1 NEMA 2 UL 508 NEMA 3R UL 508 NEMA 4 UL 508 NEMA 4X UL 508 NEMA 12 UL 508 NEMA 12K UL 508

## Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156914
Returnability	Yes
Country of origin	IT

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.56 In (6.5 cm)
Package 1 Width	2.56 In (6.5 cm)
Package 1 Length	2.56 In (6.5 cm)
Package 1 Weight	2.33 Oz (66.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	5.91 In (15.0 cm)
Package 2 Width	11.81 In (30.0 cm)
Package 2 Length	15.75 In (40.0 cm)
Package 2 Weight	6.54 Lb(US) (2.965 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

Product Life Status : **Commercialised**