

Product data sheet

Characteristics

VLSH4S5R

Disconnect switch, TeSys VLS, protruding rotary handle, screw mounting, 48x48 mm, red handle, 5 mm shaft

Product availability: Stock - Normally stocked in distribution facility

Price*: 30.82 USD



Main

Range	TeSys
Device short name	VLSH
Product or Component Type	Rotary handle
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 padlock 0.16...0.31 in (4...8 mm)
Marking	0 - 1

Complementary

Fixing mode	By 4 screws
Tightening torque	20.36 Lbf.In (2.3 N.m)
Base dimension	48 x 48 mm
Height	1.89 In (48 mm)
Width	1.89 In (48 mm)
Depth	1.54 In (39 mm)
Net Weight	0.16 Lb(US) (0.073 kg)

Environment

IP Degree of Protection	IP65
NEMA degree of protection	NEMA 1 NEMA 2 UL 508 NEMA 3R UL 508 NEMA 4 UL 508 NEMA 4X UL 508 NEMA 12 UL 508 NEMA 12K UL 508

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156945
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 In (3.0 cm)
Package 1 Width	1.97 In (5.0 cm)
Package 1 Length	3.54 In (9.0 cm)
Package 1 Weight	1.34 Oz (38.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	5.91 In (15.0 cm)
Package 2 Width	11.81 In (30.0 cm)
Package 2 Length	15.75 In (40.0 cm)
Package 2 Weight	4.35 Lb(US) (1.975 kg)

Offer Sustainability

RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status : **Commercialised**